




Classic Pull-out




Classic End Cap



Classic Splice




Classic Track




Spool Pop-out Carrier

Installation Hardware



Tamper Proof Screws



Tamper Proof Drill Bits

COMPONENTS

Cubicle Track:

Cube Care Classic Track
Clear Anodized Aluminum – Satin Finish

Carrier:

Spool Pop-out Carrier
The hook portion releases, allowing the curtain to fall. Use for safety in psychiatric care areas and correctional facilities disengages at +/- 20 lbs. of pressure

Other Parts:

Classic Pull-Out, Classic End Cap, Classic Splice & Classic Track.

SPECIFICATIONS

- > Section size: 1-3/8" x 3/4" x 0.06 wall thickness
- > Extruded 5052 anodized aluminum
- > Ridge-grooved center for easy installation
- > 20' track length bends approx. 14"
- > 3 lbs. max. weight per foot
- > 10-15% of cubicle curtain to be accommodate by carriers

Stacking: Curtain stack depth typically 3" for every foot of cubicle width. Depth may vary due to fabric type, mesh selection, and lining thickness (if selected).

Grommeting: Grommets are recommended to be spaced every 6" on-center.

**PSYCH CARE TRACKS
SPOOL POP-OUT
CARRIER FORM**

Project:

Date:

Scale:

Dimensions:

By:
